

GSWX-26

SM Cylindrical Watch Crystal


- Low cost
- Formed leads for SM
- Industrial temperature range
- Miniature size for high density applications



CONFIGURABLE OPTIONS

Parameter Option Code

PACKAGE DRAWING



ORDERING INFORMATION

To request a quotation for the GSWX-26 please use the configurable options form to choose the options you require and then submit your configured product to our team. Our expert advisers are always happy to help with your requirements and can be contacted on +44 1460 256 100 or at sales@golledge.com.

Following product selection you will be issued with a seven character Golledge part number. Your Golledge part number is the internationally accepted Golledge manufacturing part number (MPN) that should be used for all project documentation, including bills of materials (BoMs) and purchase orders.

If you have any queries regarding any of our documentation our dedicated sales team will be happy to help.

HANDLING & STORAGE



Human Body Model (HBM) 1A (250V to < 500V)

Moisture Sensitivity Level (MSL): 1

CONSTRUCTION

Press seal cylinder



COMPLIANCE



P6 Lead-free (< 0.1% by weight)



RoHS compliant with no exemptions.