

GSX-323

SM Crystal for Bluetooth

- Ideal for Bluetooth / Wireless applications
- Seam sealed for excellent stability
- Ultra-miniature for maximum space saving
- Metal lid can be grounded to minimise EMI




CONFIGURABLE OPTIONS

Parameter

Option Code

PACKAGE DRAWING



ORDERING INFORMATION

To request a quotation for the GSX-323 please use the configurable options form to choose the options you require and then submit your configured product to our team. Our expert advisers are always happy to help with your requirements and can be contacted on +44 1460 256 100 or at sales@golledge.com.

Following product selection you will be issued with a seven character Golledge part number. Your Golledge part number is the internationally accepted Golledge manufacturing part number (MPN) that should be used for all project documentation, including bills of materials (BoMs) and purchase orders.

If you have any queries regarding any of our documentation our dedicated sales team will be happy to help.

Dimensions in mm



MARKING

Г


	FREQUENCY DO T DC				
Year		2014			
	2017	2018	2019	2020	
Code	J	1	J	Ţ	

TAPE & REEL SPECIFICATION

Marking type: Laser	
DC = Date code	

DC = Date code in WY Week codes: A ~ Z: weeks 1 to 26 a ~ z: weeks 27 to 52 e.g.: "dl" = week 30 2018

SOLDERING PROFILE



Solderability limits:

260°C max x 10sec max x 2 max

2.0 2.0 1.75 1.0Ø 1.5Ø 0.3 ±0.05 7 3.5 ±0.05 5 8.0 ±0.3 2.7 -I.2 FEED 2.25 8.4 -0.4 < 1.5 ±0.3 120° 20.5Ø 2.50 13Ø 178Ø ±1.0 60Ø ±1.0 - \$

Dimensions in mm

HANDLING & STORAGE



Human Body Model (HBM) 1A (250V to < 500V)





CONSTRUCTION

Ceramic body with gold-plated pads Metal lid, seam sealed

COMPLIANCE



(P6) Lead-free (< 0.1% by weight)



RoHS compliant with no exemptions.



Nominal Net Mass: 13mg