

GSX-758

SM Crystal High Frequency

Fundamental


- Fundamental mode up to 315MHz
- Plasma etched inverted mesa process
- Wide pulling range (fundamental mode)
- Small & medium volumes also available •
- Custom frequencies available on short leadtimes

CONFIGURABLE OPTIONS

Parameter

Option Code

PACKAGE DRAWING






PAD 1

2


3

Crysta

Crystal Ground & lid



SOLDER PAD LAYOUT



Dimensions in mm

ORDERING INFORMATION

To request a quotation for the GSX-758 please use the configurable options form to choose the options you require and then submit your configured product to our team. Our expert advisers are always happy to help with your requirements and can be contacted on +44 1460 256 100 or at sales@golledge.com.

Following product selection you will be issued with a seven character Golledge part number. Your Golledge part number is the internationally accepted Golledge manufacturing part number (MPN) that should be used for all project documentation, including bills of materials (BoMs) and purchase orders.

If you have any queries regarding any of our documentation our dedicated sales team will be happy to help.



MARKING


FREQUENCY DC PARTNO

Marking type: Laser


DC = Date Code in YM, eg. "GF" = Jun 2017

	Α	В	С	D	Е	F	G	н	J	K	L	М
Υ	1	2	3	4	5	6	7	8	9	0		
м	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec

SOLDERING PROFILE



TAPE & REEL SPECIFICATION



CONSTRUCTION

Ceramic body with gold-plated pads Metal lid, seam sealed

HANDLING & STORAGE



Human Body Model (HBM) 1A (250V to < 500V)



Moisture Sensitivity Level (MSL): 1

COMPLIANCE



Lead-free (< 0.1% by weight)



RoHS compliant with no exemptions.