

# GSX49-3

## SM Crystal


- Industry standard HC49 footprint
- Low profile case for close board stacking
- Wide frequency range
- Fundamental mode available up to 50.0MHz
- Low cost



## CONFIGURABLE OPTIONS

Parameter	Option Code
-----------	-------------

## PACKAGE DRAWING




## ORDERING INFORMATION

To request a quotation for the GSX49-3 please use the configurable options form to choose the options you require and then submit your configured product to our team. Our expert advisers are always happy to help with your requirements and can be contacted on +44 1460 256 100 or at [sales@golledge.com](mailto:sales@golledge.com).

Following product selection you will be issued with a seven character Golledge part number. Your Golledge part number is the internationally accepted Golledge manufacturing part number (MPN) that should be used for all project documentation, including bills of materials (BoMs) and purchase orders.

If you have any queries regarding any of our documentation our dedicated sales team will be happy to help.

## MARKING



Marking type: Laser

## HANDLING & STORAGE



Human Body Model (HBM) 1A (250V to < 500V)



Moisture Sensitivity Level (MSL): 1

## CONSTRUCTION

Metal package, hermetic seal Insulating base, formed leads

## COMPLIANCE



Lead-free (< 0.1% by weight )



RoHS compliant with no exemptions.



Nominal Net Mass: 450mg