

# GXO-7500G

# 7050 Tight stability / high freq osc

- High precision with tight stability options
- Wide operating temperature ranges
- High frequency fundamental no multiplier
- Low & medium volumes also available
- Enable / disable tristate function



# **CONFIGURABLE OPTIONS**

Parameter Option Code

### **ORDERING INFORMATION**

To request a quotation for the GXO-7500 please use the configurable options form to choose the options you require and then submit your configured product to our team. Our expert advisers are always happy to help with your requirements and can be contacted on +44 1460 256 100 or at <a href="mailto:sales@golledge.com">sales@golledge.com</a>.

Following product selection you will be issued with a seven character Golledge part number. Your Golledge part number is the internationally accepted Golledge manufacturing part number (MPN) that should be used for all project documentation, including bills of materials (BoMs) and purchase orders.

If you have any queries regarding any of our documentation our dedicated sales team will be happy to help.

#### **ENABLE / DISABLE FUNCTION**

Input (pad 1)	Output (pad 3)					
Open	Enabled					
'1' level	Enabled					
'O' level	High Impedance					



#### **MARKING**


FREQUENCY DC PART NO

Marking type: Laser


#### DC = Date Code in YM, eg. "GF" = Jun 2017


	Α	В	С	D	Ε	F	G	Н	J	K	L	М
Υ	1	2	3	4	5	6	7	8	9	0		
М	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec

## **SOLDERING PROFILE**



#### **TAPE & REEL SPECIFICATION**





Dimensions in mm

#### **HANDLING & STORAGE**



Human Body Model (HBM) 1A (250V to < 500V)



Moisture Sensitivity Level (MSL): 1



# **CONSTRUCTION**

Ceramic body with gold-plated pads Metal lid, seam sealed

# **COMPLIANCE**



Lead-free (< 0.1% by weight)



RoHS compliant with no exemptions.